

Shielded Power Inductors – MSS7341



- 6.6 × 6.6 mm footprint; 4.1 mm high shielded inductors
- Low DCR and excellent current handling
- AEC-Q200 qualified

Designer's Kit C385 contains 3 each of all values.

Core material Ferrite

Core and winding loss See www.coilcraft.com/coreloss

Terminations RoHS compliant matte tin over nickel over phos bronze (current production) or gold over nickel over phos bronze (prior production). Other terminations available at additional cost.

Weight: 0.61 – 0.67 g

Ambient temperature –40°C to +85°C with (40°C rise) Irms current.

Maximum part temperature +125°C (ambient + temp rise). [Derating](#).

Storage temperature Component: –40°C to +125°C.

Tape and reel packaging: –40°C to +80°C


Resistance to soldering heat Max three 40 second reflows at +260°C, parts cooled to room temperature between cycles

Moisture Sensitivity Level (MSL) 1 (unlimited floor life at <30°C / 85% relative humidity)


Packaging 300/7 reel; 1200/13" reel; Plastic tape: 16 mm wide, 0.35 mm thick, 12 mm pocket spacing, 4.5 mm pocket depth

PCB washing Tested to MIL-STD-202 Method 215 plus an additional aqueous wash. See [Doc787_PCB_Washing.pdf](#).

Typical L vs Current



Typical L vs Frequency





Shielded Power Inductors – MSS7341

| Part number ¹ | Inductance ² (μ H) | Percent tolerance ³ | DCR (Ohms) | | SRF typ ⁴ (MHz) | Isat (A) ⁵ | | | Irms (A) ⁶ | |
|--------------------------|---------------------------------------|--------------------------------|------------|-------|-------------------------------|-----------------------|----------|----------|-----------------------|-----------|
| | | | typ | max | | 10% drop | 20% drop | 30% drop | 20°C rise | 40°C rise |
| MSS7341-332_L_ | 3.3 | 30,20 | 0.014 | 0.018 | 85 | 2.74 | 3.28 | 3.72 | 3.95 | 5.00 |
| MSS7341-502_L_ | 5.0 | 30,20 | 0.018 | 0.023 | 49 | 2.30 | 2.82 | 3.16 | 3.40 | 4.70 |
| MSS7341-622_L_ | 6.2 | 30,20 | 0.024 | 0.027 | 42 | 2.18 | 2.66 | 2.98 | 3.05 | 4.30 |
| MSS7341-742_L_ | 7.4 | 30,20 | 0.027 | 0.031 | 35 | 1.92 | 2.32 | 2.56 | 2.80 | 4.10 |
| MSS7341-872_L_ | 8.7 | 30,20 | 0.029 | 0.034 | 33 | 1.78 | 2.12 | 2.36 | 2.80 | 3.90 |
| MSS7341-103ML_ | 10 | 20 | 0.032 | 0.038 | 32 | 1.64 | 1.92 | 2.10 | 2.80 | 3.80 |
| MSS7341-123ML_ | 12 | 20 | 0.040 | 0.050 | 27 | 1.48 | 1.76 | 1.92 | 2.45 | 3.30 |
| MSS7341-153ML_ | 15 | 20 | 0.047 | 0.055 | 26 | 1.36 | 1.60 | 1.78 | 2.05 | 3.00 |
| MSS7341-183ML_ | 18 | 20 | 0.065 | 0.075 | 25 | 1.20 | 1.46 | 1.62 | 1.85 | 2.65 |
| MSS7341-223ML_ | 22 | 20 | 0.074 | 0.082 | 22 | 1.02 | 1.26 | 1.42 | 1.70 | 2.35 |
| MSS7341-273ML_ | 27 | 20 | 0.091 | 0.109 | 19 | 1.00 | 1.14 | 1.22 | 1.50 | 2.10 |
| MSS7341-333ML_ | 33 | 20 | 0.104 | 0.124 | 17 | 0.91 | 1.04 | 1.16 | 1.50 | 1.95 |
| MSS7341-393ML_ | 39 | 20 | 0.115 | 0.130 | 15 | 0.85 | 1.01 | 1.12 | 1.50 | 1.90 |
| MSS7341-473ML_ | 47 | 20 | 0.127 | 0.155 | 14 | 0.74 | 0.92 | 1.00 | 1.50 | 1.85 |
| MSS7341-563ML_ | 56 | 20 | 0.174 | 0.202 | 11 | 0.68 | 0.80 | 0.87 | 1.25 | 1.60 |
| MSS7341-683ML_ | 68 | 20 | 0.236 | 0.250 | 9.6 | 0.62 | 0.73 | 0.80 | 1.00 | 1.35 |
| MSS7341-823ML_ | 82 | 20 | 0.257 | 0.290 | 8.5 | 0.57 | 0.66 | 0.72 | 1.00 | 1.25 |
| MSS7341-104ML_ | 100 | 20 | 0.286 | 0.310 | 7.2 | 0.54 | 0.64 | 0.71 | 0.90 | 1.15 |
| MSS7341-154ML_ | 150 | 20 | 0.438 | 0.475 | 6.0 | 0.45 | 0.53 | 0.58 | 0.86 | 1.14 |
| MSS7341-224ML_ | 220 | 20 | 0.660 | 0.710 | 5.0 | 0.35 | 0.41 | 0.47 | 0.57 | 0.78 |
| MSS7341-474ML_ | 470 | 20 | 1.21 | 1.45 | 3.0 | 0.24 | 0.28 | 0.32 | 0.43 | 0.57 |
| MSS7341-684KL_ | 680 | 10 | 1.85 | 1.98 | 2.5 | 0.22 | 0.27 | 0.29 | 0.42 | 0.56 |

1. When ordering, specify **tolerance, termination and packaging** codes:

MSS7341-684KLD

Tolerance: M= 20%, N = 30% (Table shows stock tolerances in bold.)

Termination: L = RoHS compliant matte tin over nickel over phos bronze
Special order: T = RoHS tin-silver-copper (95.5/4/0.5) over gold over nickel over phos bronze
 or S = non-RoHS tin-lead (63/37) over gold over nickel over phos bronze.



Packaging: C = 7" machine-ready reel. EIA-481 embossed plastic tape. Special order (300 parts per full reel). Quantities less than full reel available: in tape (not machine ready) or with leader and trailer (\$25 charge).

D = 13" machine-ready reel. EIA-481 embossed plastic tape (1200 parts per full reel).


B = Less than full reel. In an effort to simplify our part numbering system, Coilcraft is eliminating the need for multiple packaging codes. When ordering, simply change the last letter of your part number from B to C.

- Inductance measured at 100 kHz, 0.1 Vrms, 0 Adc using a Coilcraft SMD-A fixture in an Agilent/HP 4263B LCR meter.
- Tolerances in bold are stocked for immediate shipment.
- SRF measured using an Agilent/HP 8753D network analyzer and a Coilcraft SMD-D test fixture.
- DC current at 25°C that causes the specified inductance drop from its value without current. [Click for temperature derating information.](#)
- Current that causes the specified temperature rise from 25°C ambient. This information is for reference only and does not represent absolute maximum ratings. [Click for temperature derating information.](#)
- Electrical specifications at 25°C. Refer to Doc 362 "Soldering Surface Mount Components" before soldering.


Typical Temperature Rise vs Current



Parts manufactured prior to Sept. 2007 were marked with only the dash number.



* Dimensions are of the case not including the termination. For maximum overall dimensions including the termination, add 0.02 in / 0.51 mm.



Recommended Land Pattern

Dimensions are in $\frac{\text{inches}}{\text{mm}}$



US +1-847-639-6400 sales@coilcraft.com
 UK +44-1236-730595 sales@coilcraft-europe.com
 Taiwan +886-2-2264 3646 sales@coilcraft.com.tw
 China +86-21-6218 8074 sales@coilcraft.com.cn
 Singapore +65-6484 8412 sales@coilcraft.com.sg

Document 383-2 Revised 09/18/24
 © Coilcraft Inc. 2025
 This product may not be used in medical or high risk applications without prior Coilcraft approval. Specification subject to change without notice. Please check web site for latest information.